



Haynes® 282®

ASTM B637 / N07208

MATERIAL DATA SHEET



MATERIAL DATA SHEET

Haynes® 282®

ASTM B637 / N07208

MATERIAL


Haynes® 282® developed by Haynes International Inc. is a nickel-based, gamma-prime strengthened superalloy which reaches impeccable properties for high-temperature structural applications. Being thermally stable with an excellent creep strength paved the way into all kinds of turbine applications within aerospace, space, and energy.

CHEMICAL COMPOSITION

Haynes® 282® ¹																		
	Ni	Cr	Co	Mo	Ti	Al	Fe	Mn	Si	C	B	P	S	Zr	Cu	Ta	Nb	W
Min.	Bal.	18.5	9.0	8.0	1.9	1.38				0.04	0.003							
Max.		20.5	11.0	9.0	2.3	1.65	1.5	0.3	0.15	0.08	0.010	0.015	0.015	0.020	0.1	0.1	0.2	0.5

POWDER PROPERTIES

Particle Size ¹	10 -45 µm
Mass Density ²	≈ 8.3 g/cm ³
Particle Shape ³	Spherical



MATERIAL DATA SHEET

Haynes® 282®


ASTM B637 / N07208

NIKON SLM® PARAMETERS

It only takes 3 tools to make you successful with metal additive manufacturing:

1. The **NIKON SLM® machine** fitting your needs,
2. The **metal powder** that defines the later purpose and functionality of a part,
3. Precisely engineered **NIKON SLM® parameters** as the missing link.

Our open parameters are the result of our vast experience in multi-laser technology and a diligent development and qualification procedure. They are key to produce fully functional parts with properties you can expect and rely on – whether you are new to AM or a large-scale production operator. We offer them to you in the following categories: **Precision (PREC)** for high-resolution complex details, **Prime (PRIM)** for balanced properties with improved productivity and **Productivity (PROD)** for the highest build rates. Pushing boundaries is in our work culture, we can also offer a new dimension of productivity on selected materials with **Productivity+ (PROD+)** and **Productivity++ (PROD++)** parameters.




MATERIAL QUALIFICATION

As one of the inventors of the selective laser melting process, we impose the most comprehensive test procedures on ourselves: hundreds of samples, multiple systems, various powder batches, numerous heat-treatments, machined vs. near-net-shape tensile specimens, several surface roughness conditions and angles, fatigue behavior, corrosion investigation, creep testing... Did we miss anything? Get in touch with us!

MATERIAL DATA SHEET

Haynes® 282®

ASTM B637 / N07208



NXG PRIME

Parameter Set	Haynes282_NXG600_PRIM_MBP3_V1 (60 µm)
Machine Compatibility	NXG XII 600, NXG 600E (1000 W)
Validated Data Preparation	Materialise SLM Build Processor
Theoretical System Build Rate ⁴	328.3 cm³/h
Minimum Relative Density ^{5,7}	99.9 %

MECHANICAL PROPERTIES⁶

M: Mean | MIN: Minimum (95 % population coverage / 95 % confidence level)⁷

Non-heat-treated

	Tensile strength R _m [MPa]		Yield strength R _{p0.2} [MPa]		Elongation at break A [%]	
	M	MIN	M	MIN	M	MIN
Machined						
Vertical	855	805	585	570	49	40
Near-Net-Shape						
Vertical	820	795	560	535	47	43

Heat-treated (Solution annealing + Aging)⁸

	Tensile strength R _m [MPa]		Yield strength R _{p0.2} [MPa]		Elongation at break A [%]	
	M	MIN	M	MIN	M	MIN
Machined						
Vertical	1125	1065	940	920	31	19
Near-Net-Shape						
Vertical	1075	1045	885	870	27	20

HARDNESS⁹

M: Mean | MIN: Minimum (95 % population coverage / 95 % confidence level)⁷

	Vickers hardness HV10	
	M	MIN
NHT	280	265
Heat-treated ⁸	390	370

SURFACE ROUGHNESS¹⁰

M: Mean | MAX: Maximum (95 % population coverage / 95 % confidence level)⁷

	Roughness average Ra [µm]		Mean roughness depth Rz [µm]	
	M	MAX	M	MAX
As built	6	10	34	55

MATERIAL DATA SHEET

Haynes® 282®

ASTM B637 / N07208

DISCLAIMER

The properties and mechanical characteristics apply to powder that is tested and sold by Nikon SLM Solutions, and that has been processed on Nikon SLM Solutions machines using the original Nikon SLM Solutions parameters in compliance with the applicable operating instructions (including installation conditions and maintenance). The part properties are determined based on specified procedures. More details about the procedures used by Nikon SLM Solutions are available upon request.

The specifications correspond to the most recent knowledge and experience available to us at the time of publication and do not form a sufficient basis for component design on their own. Certain properties of products or parts or the suitability of products or parts for specific applications are not guaranteed. The manufacturer of the products or parts is responsible for the qualified verification of the properties and their suitability for specific applications. The manufacturer of the products or parts is responsible for protecting any third-party proprietary rights as well as existing laws and regulations.

© 2025 Nikon SLM Solutions AG. All rights reserved. Subject to change without notice.

MDS_H282_2025-05.1_EN

CONTACT

Headquarters

Nikon SLM Solutions AG
Estlandring 4
23560 Lübeck
Germany

Phone: +49 451 4060-3000

www.nikon-slm-solutions.com



NOTES

¹ With respect to powder material. Compositions stated as mass or weight percent.

² Material density varies within the range of possible chemical composition variations.

³ According to DIN EN ISO 3252:2023.

⁴ Theoretical system build rate = layer thickness x scan speed x hatch distance x number of lasers. The value represents a comparable indicator but remains a theoretical value after all. It does expressively not reflect true build rates, which are influenced by part geometry, ratio between hatch and contour areas, area of exposure, recoating times, and more.

⁵ Optical density determination at test specimens by light microscopy according to internal specification. Relative density may vary depending on part geometry, orientation, volume, and other process factors. Population coverage: 99%, confidence level: 99%.

⁶ Tensile testing was performed in accordance to DIN EN ISO 6892-1:2020 B and conducted at room temperature. Samples are either machined before testing or tested in near-net-shape without any surface finishing (geometry according to DIN 50125:2022-08 C6x30). Samples labelled "Horizontal" correspond to a polar angle of $\theta = 90^\circ$; samples labelled "vertical" correspond to a polar angle of $\theta = 0^\circ$ (DIN EN ISO/ASTM 52921). Values include overlap samples, i.e. multiple lasers work simultaneously on one specimen. All data is derived from standardized SLM Solutions qualification jobs. Samples are built out of both virgin powder as well as used powder. Population coverage: 95%, confidence level: 95%.

⁷ Minimum or maximum values are set by using tolerance interval method, which is a statistical approach based on the input of population coverage (PC) and confidence level (CL). Tolerance intervals ensure that a certain percentage of samples within a batch will be above the minimum value or below the maximum value with a certain probability, e.g. the probability that 95% of all samples will be above the minimum value or below the maximum value (within a defined batch and tested according to mentioned specifications) is 95%.

⁸ Annealing was made at 1135 °C (2075 °F) +/-14 °C (25 °F) in vacuum for 45 min +/-4 min and then cooled in nitrogen gas at a rate equivalent to or faster than air cooling. The parts were then aged at 1010 °C (1850 °F) +/-8 °C (46 °F) in vacuum for 2 hours, with cooling in nitrogen gas to room temperature, and then subsequent aging at 788 °C (1450 °F) +/-8 °C (46 °F) for 8 hours in vacuum, with cooling in nitrogen gas to room temperature.

⁹ Hardness testing according to DIN EN ISO 6507-1:2024. Measurement direction "2" according to VDI 3405 2.1. Values include overlap samples, i.e. multiple lasers work simultaneously on one specimen. All data is derived from standardized SLM Solutions qualification jobs. Samples are built out of both virgin powder as well as used powder.

¹⁰ Roughness measurement on vertical walls according to DIN EN ISO 21920-3:2022; $\lambda_c = 2.5$ mm. Glass bead blasting is an additional post-processing step after corundum blasting. Values include overlap samples, i.e. multiple lasers work simultaneously on one specimen. All data is derived from standardized SLM Solutions qualification jobs. Samples are built out of both virgin powder as well as used powder.